# HORIBA

Checking zero point & diluting span gas sources Calibration of Ambient Air Monitoring Systems

## Zero Gas Generator ZNV-7

HORIBA's compact designed Zero Gas Generator ZNV-7 is used for mobile, stationary or laboratory scale zero point checking & diluting span gas sources for the calibration of ambient air analyzers.



HORIBA Europe's Zero Gas Generator ZNV-7 has been developed to check the zero point and dilute the span gas sources in order to carry out the calibration of ambient air monitoring systems. The increasing sensitivity of ambient air analyzers is required by strict official guidelines, which demands pure and dry air in a sufficient quantity at constant pressure.



## **Functions:**

- Ambient air will be sucked through a filter by using an oilfree piston compressor and will be compressed to max. 7 bar.
- The compressed air will be piped to a cooling spiral followed by coaling filter for eliminating the humidity.
- The dew point of the gas will be reduced by 35°K using a membrane dryer.
- The installed container with 7l size will reduce the operation The pressure of the container and the outlet will be hours to a minimum.


- The pressure at the outlet can be adjusted in a range of 1 – 4 bar.
- For cleaning the gas will pass filter cartridges and the Purafill filter after pressure regulating.
- The maintenance interval depends on ambient air conditions and zero gas consumption. At least 4 month will be guaranteed.
- displayed at the front panel.

## Explore the future

## HORIBA

Specifications	
Model	ZNV-7
Application	Zero point and span gas dilution
Zero gas supply	max. 10 l /min
Relative humidity	< 5 %
Efficiency for SO <sub>2</sub>	< 1.0 ppb
Efficiency for NO / NO <sub>2</sub>	< 1.0 ppb
Efficiency for O <sub>3</sub>	< 1.0 ppb
Efficiency for CO	< 10.0 ppb
Output pressuregas	0 - 4 bar
Automatic dehumidifier	
Automatic condensate drain	
Oil free piston compressor	
Power consumption	max. 435 W
Power supply	230 V ac 50 / 60 Hz
Dimensions ( L x H x W )	19" plug-in unit, 6 HU, 860 x 270 x 480 mm
Weight	30 kg
Conforming standards	CE marking, DIN EN 14792

#### External dimensions



Please read the manual before using this product to assure safe and proper handling of the product.

The contents of this data sheet are subject to change without prior notice, and without any subsequent liability to this company.
It is strictly forbidden to copy the content of this data sheet in part or in full.

Manufactured by HORIBA Europe GmbH Office Leichlingen

#### Contact Adress:

#### HORIBA Europe GmbH Office Leichlingen

Julius-Kronenberg-Strasse 9 42799 Leichlingen (Germany) Phone : +49 (0) 2175 8978-0 Fax : +49 (0) 2175 8978-50

#### HORIBA Europe GmbH Head Office

Hans-Mess-Strasse 6 61440 Oberursel (Germany) Phone : +49 (0) 6172 1396-0 Fax : +49 (0) 6172 1373 85

http://www.horiba.com

## Explore the future

## HORIBA